



Model 20 GT

# Premium Performance

The Model 20 HT/GT units feature a gearbox designed specifically for agitator service. Available in right angle (HT) and parallel shaft (GT) configurations, this rugged performer can be tailored to meet virtually any process, from critical chemical reactor systems to storage applications.

Combining the benefits of the HT and GT time proven agitators into a modular design package,

the Mixing Technologies Group of NOV provides solutions to optimize your mixing applications today and flexibility to handle your changing requirements in the future.

The Model 20 HT/GT is designed to meet AGMA, OSHA, ANSI, IEC, DIN, EU and ATEX standards and requirements.

# How is the Chemineer Model 20 HT/GT Gearbox Superior?

#### **Output Shaft Requirements**

Commercial gearboxes usually have smaller output shafts that are poorly suited for agitator duties, leading to higher gear deflections, more noise and lower reliability. For optimum mechanical integrity, it is beneficial to design the low speed shaft so that the shaft diameter between the bearings is large and the distance between the bearings is small.

Commercial gearboxes tend to use smaller shaft diameters, resulting in the need to select larger and more expensive units to handle the bending moments associated with overhung loads.

The Chemineer Model 20 HT/GT also has an oversized output shaft, which reduces gear deflection and noise, with a true cast dry well seal to avoid the risk of leaking lubricant down the shaft.

#### **AGMA Ratings when Applied to Agitators**

The Chemineer Model 20 HT/GT gearbox is unique and superior because it is designed specifically for agitator duties.

AGMA established a general purpose standard intended to be applied to gearboxes used in a wide range of industrial applications. Agitators have particular duties that make reliance on AGMA service factors inappropriate.

A standard commercial gearbox tends to use smaller shafts and larger bearing spans that result in higher deflection, wear and shorter lifespan. To obtain adequate drive life a high service factor must be applied. In comparison with a general purpose gear drive of the same nominal AGMA torque rating, the Model 20 HT/GT has much longer bearing and gear lives, which translate to lower maintenance costs and greater productivity.



### Drive Features and Benefits

#### Features

#### Benefits

Internal Shafting	Oversized low speed shaft diameter and short bearing span	Time proven design to handle shaft/impeller bending loads Reduces deflection and gear misalignment Extends bearing and gear life						
	Recessed low speed coupling half	Simplifies installation with no requirement to install the extension shaft up through the gearbox						
Gearing	Double and triple reduction options	Double/triple reduction decreases gear loads     Lowers noise levels     Allows for non-synthetic lubrication over competitive single reduction designs						
	Helical/spiral bevel (HT) and all helical (GT)	Most efficient gearing available     Reduces energy costs						
	Case carburized gearing	• Reduces wear rate for 20+ year service life						
	Reverse rotation capability	Available option for process flexibility						
Housing and Lubrication	Cast gearbox housing	Modular design with right angle (HT) and parallel shaft (GT) configurations     Reduces noise level						
	Standard R&O oils and grease	No synthetic lubrication is required     Saves installation and maintenance costs						
	Bath lubrication	Ensures vital lubrication to gears and bearings at all operating speeds     Eliminates internal/external lubrication pumps						
	Cast dry well seal	Eliminates lubrication leaks which are common in commercial gearboxes with no dry well or bolt on designs						
	Extra seal over dry well	Keeps oil out of dry well while moving gearbox						
Bearing Design	Tapered roller output bearings with short bearing span, grease lubricated	High capacity to handle bending and thrust loads     Provides long life						
	Tapered roller/cylindrical roller bearings, oil lubricated	Ensures cool operation     Ensures long life and low maintenance						



Installed Model 20 GTs at a wastewater treatment facility

### Seal Features and Benefits

Features Benefits

reatures	Deliett?					
Drop collar shaft support during seal change	Shaft drops easily by loosening coupling bolts, and engages by tightening the coupling bolts     Shaft only drops 0.5" eliminating steady bearing disengagement     Allows for wetted parts to remain in place for seal change out					
Optional throttle bushing and debris well design	Clean fluid flush eliminates process build up in seal area improving seal life     Eliminates particle shedding from entering tank					
Swing out or spacer spool seal change designs	No need to pull shaft up through gearbox or in-tank shaft supports  No additional labor or parts required for special shaft support system  No lifting and removing of gearbox, saving labor and downtime					
Variety of seal options from major mechanical seal vendors such as John Crane, Flowserve, Chesterton and AES	Cartridge double and single seals, cartridge ChemSeals and stuffing box designs provide performance and flexibility to meet agitator sealing needs					
Seal designs include cartridge single and double seals and split seals	Reduces seal change out time and shaft wear as compared to non-cartridge (shaft mounted) designs					
Low height pedestal (swing out) and seal bearing (spacer spool) design options	Seal located close to shaft support bearings (swing out) and integral seal bearing (spacer spool) reduces shaft deflections at seal, improving life					
Optional seal shut off device	Eliminates operator exposure to hazardous vapors without draining the vessel					
Jacks-n-Rails assembly available for large diameter seals	Reduces labor time for seal change out with no extra hoists required					
Optional lip seals and stuffing boxes	Low cost lip seals available for low pressure applications     Self lubricating packing offers low maintenance sealing options for pressures up to 100 psi					



Swing out seal change



# Sealing and Mounting Options

#### Open Tank

#### • Drive Mounted to Beams

Using a heavy duty, cast housing capable of handling maximum loads, the agitator mounts readily to support beams or similar structures for common open tank applications. Auxiliary seals are an option.

#### • Pedestal Mounted to Beams

The rugged, cast iron pedestal of the agitator raises the gear drive 10 to 14 inches away from the support structure to prevent exposure of the drive to the fluid and to facilitate service.

#### Closed Tank—Seal Options

#### • Lip Seal

The spring loaded, nitrile rubber lip seal protects process fluid from contamination in lower pressure applications.

#### Stuffing Box

The six ring stuffing box utilizes standard PTFE/graphite-braided packing requiring no lubrication. Optional packing materials are available.

#### • Single Mechanical Seal

The single dry running mechanical seal is the economical choice where a pressurized barrier between the tank contents and the outside environment is not necessary.

#### • Single Mechanical Cartridge ChemSeal


 $The single \ mechanical \ seal \ offers \ dry \ running \ capability \ with \ an \ easily \ replaceable \ cartridge.$ 

#### • Split Mechanical Seal


The two piece design simplifies installation and maintenance.

#### • Double Mechanical Cartridge ChemSeal

Double mechanical cartridge seals offer excellent sealing capabilities, long life and minimum maintenance. An appropriate barrier fluid keeps tank contents from escaping.




Stuffing Box



Single Mechanical Seal



Single Mechanical Cartridge ChemSeal



Split Mechanical Seal



Double Mechanical Cartridge ChemSeal

# Shaft Design

Both process and mechanical considerations determine shaft design. Shafts are sized to resist torsional loads and bending moments induced by hydraulic forces acting on the impeller, as well as to avoid excessive vibration due to the coincidence of critical frequencies and operating speed.

Shafting is straightened to tight tolerances for long seal life and smooth operation — less than 0.003 inches total run out per foot of shaft length (0.25 mm per meter).

Custom couplings, impellers, shafts and steady bearings are available upon request, including sanitary designs.

#### Types

Shafting is supplied in a single piece design or in rigidly coupled sections for easy installation. For large diameter shafts, pipe shafting is a viable option with couplings and impeller hubs welded to the shafting. A wide range of materials and coating options are available.

#### Couplings

To facilitate assembly in the field, extension shafts are attached to the drive shaft with flanged rigid couplings, eliminating the need for shafts to be installed through the gearbox. Optional in-tank couplings can either be removable tapered bore or welded simplifying installation of long shaft agitators.

#### **Steady Bearings**

Steady bearings are available to help support extremely long shafts when requested or required. Tripod, bracket and pad type steady bearings are standard design options.

#### **Extended Keyways**

Extended keyways for adjusting impeller location offer process and design flexibility.



Welded Coupling



Removable Coupling



Tripod Steady Bearing



Bracket Steady Bearing



Installed Model 20 agitators on an oil rig




# Impeller Technology



Our impeller technology is effectively applied across any spectrum of applications ensuring successful, repeatable results from lab scale to full scale operations.

Our mixing expertise includes high flow, low shear liquid-liquid agitation, solids suspension, gas dispersion, high shear blending and viscous mixing. Whether it is R&D or production phase, we have the expertise to solve your mixing challenges.











RL-3






JT-2


# **Dimensions**


### Agitator Dimensions


						Bolt Pattern	Spacer	Swivel		
Case Size	se Size A B C D		D	E	F	G	G		J	
21GT	1.18"	13.94"	6.94"	2.94"	5.71"	8" — 150# ANSI (holes straddle center line)	26.19"	10.00"	0.75"	9.50"
22GT	1.38"	18.00"	8.00"	4.00"	7.48"	10" — 150# ANSI (holes on center line)	29.82"	12.50"	0.88"	10.00"
23GT 1.58" 18.	18.63"	8.63"	4.63"	9.45"	12" — 150# ANSI (holes straddle center line)	NSI (holes straddle center line) 33.94"		1.18"	10.83"	
	10.03	0.03	4.03	9.45	14" — 150# ANSI (holes straddle center line)	N/A	14.06"	1.46"	12.80"	
21HT	1.18"	13.94"	6.94"	2.94"	5.71"	8" — 150# ANSI (holes straddle center line)	26.19"	10.00"	0.75"	9.50"
22HT	1.38"	18.00"	8.00"	4.00"	7.48"	10" — 150# ANSI (holes on center line)	29.82"	12.50"	0.88"	10.00"
23HT 1.58"	58" 18.63" 4.63" 4.63"	FOII 10 COII	0.63"	4.62"	9.45"	12" — 150# ANSI (holes straddle center line)	33.94"	N/A	1.18"	10.83"
		9.45	14" — 150# ANSI (holes straddle center line)	N/A	14.06"	1.46"	12.80"			

- $\textbf{1} \ \, \textbf{Agitator output speed, shaft diameter and extension, impeller design and other optional features to suit application} \\$
- 2 Alternate flange sizes are available









GT/HT A, L, N, NC, NS & NT (N, NC & NS drives swivel)




### Swivel Dimensions


Case Size	K	L
21GT	11.18"	17.57"
22GT	17.50"	22.61"
23GT	21.90"	28.31"
21HT	9.84"	17.57"
22HT	12.56"	22.61"
23HT	16.61"	28.51"

# Typical Drive Assembly Swivel Dimensions

Drive assembly pivots at top of pedestal to allow change out of mechanical seals. See IOM for special motor conduit instructions.




GΤ



### Motor Dimensions

Frame Size		w		Υ							
			X	21GT	22GT	23GT	21HT	22HT	23HT		
	140	7.75"	13.11"	3.98"	_	_	6.46"	_	_		
	180	9.25"	16.24"	5.51"	6.02"	_	7.99"	9.41"	-		
	210	11.00"	17.96"	5.51"	6.02"	_	7.99"	9.41"	_		
	250	12.75"	22.25"	_	6.85"	7.01"	_	10.24"	11.43"		
NEMA	280	14.50"	24.24"	_	7.76"	7.01"	_	11.14"	11.43"		
	320	16.88"	27.00"	_	8.23"	8.27"	_	11.61"	12.69"		
	360	18.50"	27.63"	_	_	9.49"	_	_	13.91"		
	400	20.88"	31.75"	_	_	10.83"	_	_	15.25"		
IEC	80	6.61"	10.66"	3.85"	_	I –	6.06"	I –	_		
	90	7.40"	11.18"	4.13"	_	_	6.62"	Ī-	_		
	100	7.72"	13.15"	4.92"	5.35"	_	7.40"	8.74"	_		
	112	9.45"	13.03"	4.92"	5.35"	_	7.40"	8.74"	_		
	132	10.61"	16.73"	5.39"	6.22"	6.10"	7.88"	9.61"	10.52"		
	160	12.52"	21.26"	_	7.87"	7.48"	_	11.26"	11.90"		
	180	14.37"	23.31"	_	7.87"	7.48"	_	11.26"	11.90"		
	225	17.64"	30.51"	<b>-</b>	_	9.53"	_	Ī-	13.95"		
	250	20.00"	35.04"	_	_	9.53"	_	1-	13.95"		
	280	22.17"	38.39"	_	_	9.53"	_	_	13.95"		



# Drive Assembly Dimensions

Case Size	М	N	0	P	R	s	Т	U	v	z
21GT	12.77"	6.45"	0.84"	5.56"	5.56"	7.81"	17.91"	6.73"	6.69"	8.47"
22GT	16.97"	8.48"	1.00"	7.06"	7.06"	10.06"	26.00"	8.50"	9.06"	10.75"
23GT	21.97"	10.99"	1.00"	9.65"	7.68"	2.17"	31.15"	9.25"	11.41"	14.80"
21HT	12.77"	6.45"	0.84"	5.56"	5.56"	7.81"	38.75"	6.73"	5.75"	10.83"
22HT	16.97"	8.48"	1.00"	7.06"	7.06"	10.06"	59.70"	8.50"	7.23"	12.91"
23HT	21.97"	10.99"	1.00"	9.65"	7.68"	2.17"	73.47"	9.25"	9.77"	16.50"


# Chemineer Advanced Design Initiative

The Chemineer Advanced Design Initiative brings proven technical expertise to each mixing solution, from basic mixer and impeller design through complex process application analysis. Continuing research in both mechanical and process aspects of mixing allows us to provide high quality and high value products and services. Combined with proprietary data evaluation methodology and extensive field experience, we provide the most accurate application evaluation possible. Let us optimize your application, saving you time and money, by applying our experience and state of the art tools, such as:


 High tech customer test laboratory—offers the most advanced testing techniques in the industry specific to your process

- R&D laboratory—provides advanced process and mechanical research which is incorporated into custom design packages to optimize your application
- Computational Fluid Dynamics (CFD)—provides visual projections of mixer performance by generating a series of mathematical models of fluid flows
- Digital Particle Image Velocimetry (DPIV)—provides instantaneous flow visualization and quantitative measurement of the fluid velocity field
- Laser Doppler Anemometry (LDA) corroborates time averaged DPIV data, especially for velocity fields in the vicinity of the impeller
- Laser Induced Fluorescence (LIF)—enables the user to gain a fundamental understanding of mixing by tracking the path and diffusion of injectants in agitated vessels and static mixers

- CEDS™ (Chemineer Expert Design System)—the industry leader in agitator design and analysis software. This proprietary program suite optimizes process performance, in addition to mechanical integrity, strength and reliability
- ChemScale<sup>™</sup>—the industry standard method for effective mixer selection that helps to optimize the agitator design for your specific process needs
- Finite Element Analysis (FEA)—
   dynamic vibrational and stress
   analysis of vessel and agitator
   support structures ensures proper
   design to handle agitator loads.
   Product design tool for stress and
   deformation analysis ensures
   product safety and reliability
- CAD and SolidWorks 3D Design state of the art product and job design software, with customer specific mixer drawings available
- A library of technical articles available on our website



Example of CFD modeled flow fields



Example of FEA analysis



# Aftermarket Parts and Services

At NOV we offer customers immediate assistance to help achieve operating performance goals for agitation and mixing processes. This is accomplished in two ways: ensuring replacement parts and services are available in a timely manner to increase the "uptime" of your systems, and ensuring customers are offered the latest technology to improve the performance of agitation and mixing systems.

#### The Right Part Every Time

We provide drop in replacement parts of standard and custom Chemineer agitator components, minimizing installation problems like improper fit up or alignment. Chemineer replacement parts are made to original equipment specifications to ensure maximum reliability of your mixing equipment.

#### **Technical Support**

Our technical support is just a phone call away. Whether you need assistance with installation, startup, maintenance, or replacement parts, our technical experts are ready to help.

Field service technicians are ready to assist your crew with installation, troubleshooting, reliability audits, or maintenance and operator training in your facility.

#### Installation

We offer expert help on installation, whether your application requires one or multiple agitators. Field service technicians can quickly and efficiently supervise the installation and start up of your agitator or complete the installation from start to finish.

#### **Authorized Service Centers**

We offer multiple options to get your process back up and running. Highly trained field service technicians are ready to deploy for assisting maintenance crews in repair, diagnostic, and/or maintenance work. An authorized service center is located near your plant for quick responsiveness backed by the full support of our manufacturing facility.

Our field service technicians can also perform repairs and maintenance on site. Service agreements are available for routine maintenance services to keep your equipment operating at optimum performance levels. While on site, our team can perform reliability audits to review your current mixing equipment and provide recommendations

for mechanical and process improvements and critical spares planning.

The service centers located at our manufacturing facilities are utilized for more extensive failure analysis, fast replacement parts assemblies, and the most reliable agitator repair service in the world. New and refurbished parts options are available to suit your business requirements and get equipment back into operation.

We offer customer service plans tailored to fit your needs. Contact your local representative or call us directly at 937-454-3200.

#### **Parts**

Our large inventory supports your stock and provides quick fulfillment of maintenance and repair needs. Emergency stocked parts are shipped within 24 hours. In addition to a wide selection of standard replacement items such as bearings, seals and motors, we stock complete drives and internal subassemblies. Our drive exchange program offers a replacement drive for rapid conversion for Chemineer and competitive drives.

#### Warranty

For added peace of mind the Model 20 HT/GT agitator is backed by a comprehensive product warranty.

Emergency Hotline: +1 937 926 1724



 $\textit{Experienced field service technician repairing equipment on site to \textit{minimize downtime}}$ 

#### **Sales Facilities**

US Ohio +1 937 454 3200 chemineer@nov.com

US North Andover +1 978 687 0101 navinfo@nov.com

United Kingdom +44 1332 363 175 chemineeruk@nov.com

China

+86 21 6124 0001 chemineercn@nov.com

Singapore +65 6271 1121

chemineeruk@nov.com

Mexico

+52 55 3300 5370

chemineerventasmx@nov.com

Austria

+43 1 8923481

chemineeruk@nov.com

#### **Manufacturing Facilities**

US

+1 937 454 3200 chemineer@nov.com

United Kingdom +44 1332 363 175 chemineeruk@nov.com

China

+86 21 6124 0001 chemineercn@nov.com

National Oilwell Varco has produced this brochure for general information only, and it is not intended for design purposes. Although every effort has been made to maintain the accuracy and reliability of its contents, National Oilwell Varco in no way assumes responsibility for liability for any loss, damage or injury resulting from the use of information and data herein. All applications for the material described are at the user's risk and are the user's responsibility.

#### **Corporate Headquarters**

7909 Parkwood Circle Drive Houston, Texas 77036

© 2015 National Oilwell Varco | All Rights Reserved Bulletin 705 Rev 02

